



## GUIDE TO NSK AUTOMOTIVE BEARINGS FOR REPLACEMENT

### ASEAN AND OCEANIA REGION

#### Important Information, please note:

- The information presented is for general reference only, as vehicle models sold in different country may differ in their construction (transmission, gearbox, engines, etc). You are advise to verify the application for its correctness before use.
- Although care have been taken to ensure correctness of the information contained in this guide, NSK shall in no event accept liability for any damages or losses suffered due to any errors and/or omissions. We will gratefully acknowledge any additions or corrections.
- Specifications are subjected to change without notice and without any obligation on the part of the manufacturer.
- NSK has a basic policy not to export any products or technology designated as controlled items by export-related laws. When exporting the products in this guide, the laws of the exporting country must be observed
- Please contact our local representative, should you have any queries.



**AUTOMOTIVE BEARING REFERENCE FOR MODELS IN ASEAN & OCEANIA REGION**

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
<b>DAIHATSU</b>					
Ayla (D80N / D91B) <i>Same as Toyota 'Agya'</i>		2013 -	Clutch Brg	ZA-44TKZ2801B1	
Calya (D30D/D91B) <i>Same as Toyota 'Calya'</i>		2016 -	Clutch Brg	ZA-44TKZ2801B1	
Delta (U300-500/Dyna) <i>Same as Toyota "DYNA"</i>		2000 - 2012	Clutch Brg	45TKD07	BU2#.3#,4#,5# series
			Clutch Brg	68TKB3505A2RA	KDY221,231,241,271,281
			Front Wheel (In)	3578R/3525R	
			Front Wheel (Out)	02474R/02420R	
			Rear Wheel (In)	HR32212J	
			Rear Wheel (Out)	HR32213J	
Gran Max - D40D/SS (Hijet) <i>Indonesia Reference</i>		2007 - 2015	Clutch Brg	ZA-44TKZ2801B1	
			Front Wheel	ZA-38BWD21CA53**	
Taruna (X555 / J) <i>Also sold as "Taft" in Indonesia Same as Perodua "Kembara" in Malaysia</i>		2000 - 2006	Front Wheel	ZA-38BWD21CA53**	
			Rear Wheel	6307DDU	
Terios - D41N <i>See Toyota "RUSH"</i>		2010 -	Clutch Brg	ZA-44TKZ2801B1	
			Front Wheel	ZA-38BWD28DCA98-01LB (ABS)	
Zebra (432N / KM) <i>In Vietnam named "Hijet Jumbo" &amp; "Citivan"</i>		2000 - 2007	Clutch Brg	ZA-44TKB2805B/BR	(with / without clip)
			Front Wheel	HR30204J / H320/28XJ	
			Rear Wheel	6306DDU	
<b>FORD</b>					
Everest (J97 / U268)		2003 -	Front Wheel	ZA-47KWD02AU42C-01LB	
Ranger - (J97U/J97)		2006 - 2012	Clutch Brg	ZA-54TKB3604A	
			Front Wheel	ZA-47KWD02AU42C-01LB	
			Rear Wheel	HR30208J	
			Idler	58ST603DDWA1CG12**LB	Timing Belt
Ranger - (P375/T6)		2012 -	Front Wheel	ZA-47KWD03CA173-01LB (ABS) High Rider	
			Front Wheel	ZA-45KWD09CA195-01LB (ABS) Low rider	
			Rear Wheel	ZA-45KWD08CA189**LB	
Transit (V348 / V3)		2006 - 2015	Front Wheel	HR32007XJ / LM11949R/910R	
			Rear Wheel	HR32205J / HR32207J	
<b>GM / HOLDEN</b>					
Rodeo (I190/GMT335-700) (same as Isuzu D-MAX)			Front Wheel	HR32008XJ-A- / HR32009XJ-A-	
			Rear Wheel	ZA-42KWD08AU42C-01LB	
<b>HONDA</b>					
Accord (QP/D5)		2008 - 2013	Rear Wheel	ZA-60BWKH11D-Y-5	
Accord (2GA/D5)	2GA	2013 -	Rear Wheel	ZA-64BWKH22-Y-5-01	
Amaze		2014 -	Front Wheel	ZA-38BWD27ACA75-01LB (ABS)	
Brio		2014 -	Front Wheel	ZA-38BWD27ACA75-01LB (ABS)	
City - Gen4 (MN / GSP) <i>(Malaysia Reference)</i>		2003 - 2008	Clutch Brg	ZA-47TKB3102A	
			Front Wheel	ZA-38BWD26E1CA61** (ABS)	
			Rear Wheel	ZA-28BWK19B-Y-2CP	Drum Brake
			Rear Wheel	ZA-28BWK20A-Y-2CP	Disc Brake
			Idler	ZA-80SPF0310DDUL1B	Fan Belt Pulley
City - Gen5 (2PS/GSP)		2008 - 2014	Clutch Brg	ZA-47TKB3102A	
			Front Wheel	ZA-38BWD27ACA75-01LB (ABS)	

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
Civic - Gen8 (UH - C5)		2006 - 2012	Clutch Brg	ZA-47TKB3102A ZA-47TKT3101B	
			Rear Wheel (Disc)	ZA-47BWKH02L-Y-5 LB	
Civic - Gen9 (2HC/ C5)	2HC	2012 - 2016	Front Wheel	ZA-43BWD15BCA82**S01	
			Rear Wheel (Disc)	ZA-55BWKH25E-Y-01LB	
CR-V Gen1	RD1 - 3	1995 - 2001	Front Wheel	ZA-43BWD14A1CA69**	
CR-V Gen2 (KL/CS)	RD4 -7	2002 -2006	Front Wheel	ZA-45BWD12JCA85**	
			Rear Wheel	ZA-38BWD26E1CA61**	
CR-V Gen3 (WQ/C-5)	RE1 - 5, RE7	2007 - 2012	Front Wheel	ZA-51BWD01B1CA9-01LB (ABS)	
			Rear Wheel (2WD)	ZA-57BWKH02E-Y-5CP-01 (ABS) 2WD Only	
CR-V Gen4 (2WS/C-5)	RM1,3,4	2012 -	Front Wheel	ZA-51BWD01B1CA9-01LB (ABS)	
			Rear Wheel	ZA-64BWKH15N-Y-5CP01 (ABS)	
HR-V (2XP/GSP 2) <i>(also called VezeL)</i>	2XQ	2015 -	Front Wheel	ZA-51BWD01B1CA9-01LB (ABS)	
Jazz - Gen1 (F1/GSP)	GD1, GD2	2004 - 2008	Clutch Brg	ZA-47TKT3101B	
			Front Wheel	ZA-38BWD26E1CA61** (ABS)	
			Rear Wheel (2WD)	ZA-28BWK19B-Y-2CP	Drum Brake
			Rear Wheel (2WD)	ZA-28BWK20A-Y-2CP	Discs Brake
			Idler	ZA-80SPF0310F1-Y-5	Fan Belt Pulley
Jazz - Gen2 (2AP/GSP)		2008 - 2014	Clutch Brg	ZA-47TKT3101B	
			Front Wheel	ZA-38BWD27ACA75-01LB (ABS)	
Jazz - Gen3 (2WF/GSP 2)		2014 -	Clutch Brg	ZA-47TKT3101B	
Mobilio		2014 -	Front Wheel	ZA-38BWD27ACA75-01LB (ABS)	
			Rear Wheel (4WD)	ZA- 32BWD07A1CA15** (ABS)	
Odyssey 2.4 (RBI)		2003 - 2008	Rear Wheel (2WD)	ZA-57BWKH02E-Y-5CR01	
VezeL (2XP/GSP2)		2015 -	Front Wheel	ZA-51BWD01B1CA9-01LB (ABS)	
<b>HYUNDAI</b>					
Accent (RB/KP2)		2011 -	Clutch Brg	ZA-48TKZ3201A	
<b>ISUZU</b>					
Panther (I160/UCR145) <i>Called 'Crosswind' in Philippines</i>		2000 - 2016	Clutch Brg	ZA-24TK308B2	
			Front Wheel (In)	L45449R/410RNES4C*01	
			Front Wheel (Out)	LM11749RGB3/710RGB	
			Rear Wheel	40BW04C4**	
ELF (ELF/ELF)		2000 -	Clutch Brg	ZA-TK45-4B	<i>Malaysia Reference</i>
			Front Wheel (In)	3384/3320-A-	
			Front Wheel (Out)	02474R/02420R	
			Rear Wheel (In)	28985-A-R/28920R	
			Rear Wheel (Out)	28584R/28521R	
D-Max (I190/GMT355-700) <i>Australia - 'Holden Rodeo'</i>		2002 - 2011	Clutch Brg	ZA-60TKZ3201R/R1	
			Front Wheel	HR32008XJ-A / HR32009XJ-A	
			Rear Wheel	ZA-42KWD08AU42C-01LB	
D-Max (RT50/GMT355-700)		2011 - 2015	Clutch Brg	ZA-60TKZ3201R/R1	
			Clutch Brg (2WD)	ZA-48TKB3204R	2.5 Diesel
			Rear Wheel	ZA-42KWD08AU42C-01LB	
			Tensioner	ZA-76SPV39D+S05	Acc. Belt / Engine 4JK, AJJ 2.5 Diesel
<b>Mazda</b>					
CX-3	J03K	2015 -	Rear Wheel (4WD)	ZA-55BWKH29A-Y-5CP01	Sky Activ B
BT-50 (J97M/J97)		2006 - 2011	Clutch Brg	ZA-54TKB3604A	
			Front Wheel	ZA-47KWD02AU42C-01LB	
			Rear Wheel	HR30208	
			Idler	58ST603DDWA1CG12**LB	Timing Belt
BT-50 (J26E/T6)		2011 -	Front Wheel	ZA-47KWD03CA173-01LB (ABS)	High Rider
			Front Wheel	ZA-45KWD09CA195-01LB (ABS)	Low Rider
			Rear Wheel	ZA-45KWD08CA189**LB	

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
<b>Mitsubishi</b>					
Adventure /Freeeca (KZ/KZ) "Kuda" - indonesia "Jolie" - Vietnam		2002 -	Clutch Brg Front Wheel Rear Wheel	ZA-55TKA3102A M12649R/610RPNAC LM29749R/LM29710R	
Attrage Also called 'Mirage'		2012 -	Rear Wheel	ZA-28BWD08ACA28-01LB	
Canter (Canter/Canter) Indonesia Reference		2000 - 2012	Clutch Brg Front Wheel (In) Front Wheel (Out) Front Wheel (In) Front Wheel (Out) Rear Wheel (In) Rear Wheel (out)	ZA-58TKA3703B HR30210J (In) HR30207J-A- (Out) 50KW01 (In) HR32207J-A- (Out) HR30212J-A -(In) HR30211J-A-1 (Out)	(PS100) (PS100) (PS120) (PS120) (PS100 + 120) (PS100 + 120)
Canter (New) Indonesia Reference	FE71B, FE73B, FE83B	2012-	Clutch Brg Front Wheel (In) Front Wheel (Out) Rear Wheel (In) Rear Wheel (out)	Unknown 50KW01 (In) HR32207J-A- (Out) HR30212J-A -(In) HR30211J-A-1 (Out)	
Canter Malaysia Imports	FE82	2011	Clutch Brg	ZA-68TKB4701B	Malaysia Reference
Colt L300 (DE/E) Also called "L300"		2000 -	Clutch Brg Front Wheel (In) Front Wheel (Out) Rear Wheel	ZA-48TKA3210 LM48548R/510RPN4C M12649R/610RPN4C R32-10	
Grandis		2005 - 2010	Rear Wheel (4WD) Rear Wheel (2WD)	ZA-58BWKH065E2-JB--01 ZA-49BWKHS58D-Y-5C01	
Pajero		2006 - 2013	Front Wheel Front Wheel	ZA-/HO/50KWH01M-Y-01 ZA-/HO/52KWH01-Y--01	Short Body, 16" Brake Long Body, 17" Brake
Triton (CR/CR)		2005 - 2015	Front Wheel (4x2)	ZA-40KWD02U42CA-01LB	
<b>NISSAN</b>					
Navara (H61B / X61B)		2007 -	Idler	ZA-80SPPV0106+S01 LB	Access. Belt
Navara (H60B / X61B)		2014 -	Rear Wheel	ZA-/HO/45KWD10C-01LB	
Presage	U31		Front Wheel	ZA/HO/66BWKH28A-Y01	
Urvan (E25 / CY-L)		2005 -	Front Wheel Rear Wheel	ZA-/HO/51KWH01N-Y-01 HR30208J	Malaysia Reference
Urvan (E26)		2012-	Front wheel	ZA-/HO/50KWH06-Y--01	Malaysia Reference
Teana "Maxima" in Australia	J31	2004 - 2011	Front Wheel	ZA/HO/66BWKH28A-Y01	
Murano	Z50		Front Wheel	ZA/HO/66BWKH28A-Y01	
Sylphy	G11		Front Wheel Rear Wheel	ZA-/HO/62BWKH25B-Y01 ZA-/HO/44BWKH41B-Y01	
<b>PERODUA</b>					
Alza (D73B/D71A)		2009 - 2015	Clutch Brg Front Wheel	ZA-44TKZ2801B1R (w/Clip) ZA-40BWD17DCA11-01LB	Malaysia model
Axia (D87A/D91B) Replace 'Viva' Same base Alya & Agya		2014 -	Clutch Brg	ZA-44TKZ2801B1R (w/Clip)	
Bezza (D63D/D91B)		2016 -	Clutch Brg	ZA-44TKZ2801B1R (w/Clip)	
Myvi Gen1 (D73A/D71A) Also called Daihatsu 'Sirion' in Indonesia		2005 - 2011	Clutch Brg Front Wheel	ZA-44TKZ2801B1R (w/Clip) ZV-35BWD28CA47** LB	
Myvi Gen2 (D74B/D71A) Also called Daihatsu 'Sirion' in Indonesia		2011 -	Clutch Brg	ZA-44TKZ2801B1R (w/Clip)	

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
<b>PROTON</b>					
Exora 1.6 (P620A/P2)		2009 -	Front Wheel	ZA-40BWD07ACA85**	
Persona (WRM41/GX)		2007 -	Clutch Brg Front Wheel Tensioner	ZA-48TKT3202 ZA-40BWD07ACA85** 60BT06104	CamPro Engine
Saga BLM 1.3 (P211/SCM)		2008 - 2016	Clutch Brg Front Wheel Tensioner	ZA-48TKB3302B ZA-34BWD04BCA70** 60TB06104	CamPro Engine
Saga FLX 1.6			Front Wheel	ZA-34BWD04BCA70**	
<b>SUZUKI</b>					
Alto 800	YE3	2011 -	Rear Wheel	ZA-25BWD03DCA42** LF	
Alto K10	YG4	2006 -	Rear Wheel	ZA-25BWD03DCA42** LF	
Astar	YC5	2008 -	Rear Wheel	ZA-25BWD03DCA42** LF	
Wagon R <i>Indonesia =&gt; Karimum Wagon R</i>	YR9	2010 -	Rear Wheel Tensioner	ZA-25BWD03DCA42** LF ZA-70SPPV0407DDUL16	
APV (YLO : TC/TY)		2004 -	Clutch Brg Clutch Brg Front Wheel Rear Wheel	ZA-50TRZ3301 ZA-50TKB3308A ZA-35BWD24CA18** LB 6308DDU	For 'GC415'
Ertiga (YL8/YN)		2012 -	Front Wheel Tensioner	ZA-45BWD16ACA103**LB (ABS) ZA-70SPPV0407DDUL16	
Swift (Old models)		-	Rear Wheel	ZA-28BWD05ACA30**	
Swift		2010 -	Front Wheel Tensioner	ZA-40BWD21ECA116** LF (ABS) ZA-70SPPV0407DDUL16	
Swift Dzire		2010 -	Front Wheel	ZA-40BWD21ECA116** LF (ABS)	
Ciaz		2014 -	Front Wheel	ZA-40BWD21ECA116** LF (ABS)	
<b>TOYOTA</b>					
Agya (D80N / D91B) <i>Same for Daihatsu 'Ayla'</i>		2013 -	Clutch Brg	ZA-44TKZ2801B1	
Allion <i>(Gen 1 &amp; Gen 2)</i>	T240, T260	2001 -	Front Wheel Rear Wheel	ZA-40BWD12JCA88** ZA-55BWKH10-Y-5CP-01	AZT240, NZT240/260 ZZT24#, ZRT26#
Avanza - Gen 1 (794N/U-IMV) <i>Same for Daihatsu 'Xenia'</i>		2003 - 2011	Clutch Brg Front Wheel	ZA-44TKZ2801B1 ZA-30BWD10ACA36** LB	
Avanza - Gen2 (D01N/U-IMV) <i>inc. Daihatsu 'Xenia'</i>		2011 -	Clutch Brg Front Wheel Rear Wheel	ZA-44TKZ2801B1 ZA-38BWD28DCA98-01LB (ABS)	
Axio (Corolla) <i>Japan reference</i>	E140/E150	2006 - 2012	Front Wheel Rear Wheel	ZA-40BWD12JCA88** ZA-55BWKH02A-Y-5CP01	NZE14#, ZRE14#
Calya (D30D/D91B) <i>Same for Daihatsu 'Sigra'</i>		2016 -	Clutch Brg	ZA-44TKZ2801B1	
Camry (050A/MC-M)		2012 -	Front Wheel	ZA-45BWD10BCA86** LB	
Camry (043L/MC-M)		2006 - 2012	Front Wheel	ZA-45BWD10BCA86** LB	
Camry (045L/MC-M)		2006 - 2012	Front Wheel Rear Wheel	ZA-45BWD10BCA86** LB ZA-38BWD01A1-A-CA-01	
Corolla (301L/MC-C)	E140 / E150 (Gen 10)	2008 -2014	Clutch Brg Front Wheel	ZA-50TKZ3301GRA ZA-40BWD12JCA88**-01LB	Eng.: 2ZR-FE, 2NZ-FE, INZ-FE
Corolla (933N/330N)	E120 / E130 (Gen 9)	2003 -2007	Clutch Brg Front Wheel	ZA-60TKZ3502AR ZA-40BWD12JCA88**-01LB	
Corolla (079L,316N / 330N) <i>Japan Reference</i>	E120 / E130 (Gen 9)	2002 - 2007	Clutch Brg Front Wheel	ZA-60TKZ3502AR ZA-40BWD12JCA88**-01LB	

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
Dyna Rino (U300 – 500/Dyna) <i>Also sold as Daihatsu 'Delta'</i>	2000 – 2014	Clutch Brg	45TKD07	BU2#, 3#, 4# ----- series	
		Clutch Brg	68TKB35052RA	KDY221,231,241,271,281	
		Front Wheel (In)	3578R/3525R		
		Front Wheel (Out)	02474R/02420R		
		Rear Wheel (In)	HR32212J		
		Rear Wheel (Out)	HR32213J		
Fortuner (640A)	2016 –	Rear Wheel	ZA-42KWD11CA43*-01LB		
Fortuner ( 669L/IMV)	2010 – 2015	Clutch Brg	ZA-58TKZ3504A3RA		
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Front Wheel (4WD)	ZA-54KWH01R-Y-2CA-01		
		Rear Wheel	ZA-42KWD10U42CA-01LB		
		T. Idler	62TB0629B28 LB		
Tensioner	ZA-75SPF0327DDUM	Acces. Belt			
Fortuner (692L/IMV)	2005 – 2010	Clutch Brg	ZA-50TKB3504B1R		
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	40BW06CG50**		
		T. Idler	62TB0629B28 LB		
		Tensioner	ZA-75SPF0327DDUM	Acces. Belt	
Hiace (550N/GV)	2006 –	Clutch Brg	ZA-58TKB3505B1R	2.7 Diesel	
		Front Wheel	ZA-54KWH02D-Y-2CA-01		
Hilux Revo (640A/IMV) <i>Australia named "Hilux"</i>	2015 –	Rear Wheel	ZA-42KWD11CA43*-01LB		
Hilux Vigo (669L/IMV)	2008 – 2015	Clutch Brg	ZA-50TKZ3502R	L4, 2.7L Petrol	
		Clutch Brg	ZA-50TKZ3503RA	L4, 2.5L Diesel	
		Clutch Brg	ZA-58TKZ3504A3RA	L4, 3.0L Diesel	
		Clutch Brg	ZA-58TKZ3503RA	V6, 4.0L Petrol	
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	ZA-42KWD10U42CA-01LB		
		T. Idler	62TB0629B28 LB		
		Tensioner	ZA-75SPF0327DDUM	Acces. Belt	
Hilux Vigo (692N/IMV)	2005 –2008	Clutch Brg	ZA-50TKZ3502R	L4, 2.7L Petrol	
		Clutch Brg	ZA-50TKZ3503RA	L4, 2.5L Diesel	
		Clutch Brg	ZA-58TKZ3504A3RA	L4, 3.0L Diesel	
		Clutch Brg	ZA-58TKZ3503RA	V6, 4.0L Petrol	
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	40BW06CG50**		
		T. Idler	62TB0629B28 LB		
		Tensioner	ZA-75SPF0327DDUM	Acces. Belt	
Innova – 669L	2008 –	Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	ZA-42KWD10U42CA-01LB		
		T. Idler	62TB0629B28 LB		
		Tensioner	ZA-75SPF0327DDUM	Acces. Belt	
Innova – 669L <i>(Malaysia, Vietnam, Indonesia, India Only)</i>	2008 –	Clutch Brg	ZA-50TKB3504B1R		
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	HTF35BW10E-G-3CG3-01		
Innova – 692N	2005 – 2008	Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	40BW06CG50**		
		T. Idler	62TB0629B28 LB		
		Tensioner (Acc.)	ZA-75SPF0327DDUM		
Innova – 692N (VN, Isia, Ind) <i>(Malaysia, Vietnam, Indonesia, India Only)</i>	2004 – 2008	Clutch Brg	ZA-50TKB3504B1R		
		Front Wheel	ZA-43KWD07AU42C-01LB		
		Rear Wheel	HTF35BW10E-G-3CG3-01		
Kijang (630N ; 670H/KF) <i>Indonesia</i>	1997 – 2006	Clutch Brg	ZA-50TKB3504B1R		
		Front Wheel (In)	LM67048R/LM67010 (5K)		
		Front Wheel (Out)	LM11949R/LM11910R (5K)		
		Rear Wheel	35BW08C4**SA**		
Kijang (630N ; 670H/KF) <i>Indonesia</i>	4K / 5K	1986 – 1997	Clutch Brg	ZA-50TKB3504B1R	
			Front Wheel (In)	L44649R/L44610R (4K)	
			Front Wheel (In)	LM67048R/LM67010 (5K)	
			Front Wheel (Out)	LM11749RGB3/710RGB (4K)	
			Front Wheel (Out)	LM11949R/LM11910R (5K)	
			Rear Wheel	35BW08C4**SA** (5K)	
			Rear Wheel	B35-53A-AG-5C4**SA	

Vehicle Model	Model Code	Year	Fitting Position	Bearing Reference	Remarks
Landcruiser Prado (611L/F2)		2009 - 2016	Clutch Brg	ZA-50TKB3505B1R	
			Front Wheel	ZA-54KWH01R-Y-2CA-01	
Landcruiser Prado (494N/F2)	120	2002 - 2009	Front Wheel	ZA-54KWH01R-Y-2CA-01	
Premio (Gen 1 & Gen 2)	T240, T260	2001 -	Front Wheel	ZA-40BWD12JCA88**	AZT240, NZT240/260
			Rear Wheel	ZA-55BWKH10-Y-5CP-01	ZZT24#, ZRT26#
Prius	ZW30	2010 -2015	Rear Wheel	ZA-49BWKHS58D-Y-5C01	
RAV4 (120L / MC-M)		2005 - 2013	Clutch Brg	ZA-60TKB3502AR	
			Front Wheel	ZA-62BWKH10L-Y-5CP01	
			Rear Wheel (2WD)	ZA-49BWKHS40N-Y-5C01	
			Rear Wheel (AWD)	ZA-58BWKH17D-Y-5CP01	
RAV4 (410A / MC-M)		2013 - 2016	Front Wheel	ZA-62BWKH10L-Y-5CP01	
			Rear Wheel (AWD)	ZA-58BWKH17D-Y-5CP01	
Rush/ Terios (D41N / U-IMV)		2010 -	Clutch Brg	ZA-44TKZ2801B1	
			Front Wheel	ZA-38BWD28DCA98-01LB	
Soluna Vios - Gen1 (503N/NBC) <i>"Limo" Taxi in Indonesia</i>		2003 -2006	Clutch Brg	ZA-50TKZ3302BR/CR	
			Front Wheel	ZA-38BWD22LCA96-01LB	
Vios - Gen2 (482L/NBC2)	NCP93	2007 - 2012	Clutch Brg	ZA-50TKZ3302BR/CR	
			Front Wheel	ZA-40BWD17DCA11-01LB (ABS)	
			Rear Wheel	ZA-44BWKHS44B-Y-5C01 (ABS)	
Yaris (351L/NBC2)		2006 - 2014	Clutch Brg	ZA-50TKZ3301GRA	2SZ engine
			Front Wheel	ZA-40BWD17DCA11-01LB (ABS)	
			Rear Wheel	ZA-44BWKHS44B-Y-5C01	